

HIGH SPEED STEELS

Application Segments
Cutting Tools
Available Product Variants
Long Products
Product Description
BÖHLER \$607 – "The wear-resistant one" This grade has very high wear resistance while maintaining high toughness and perfectly acceptable machinability.
Process Melting
Airmelted
Properties
 > Toughness & Ductility : high > Wear Resistance : very high

- > Compressive strength : high
- > Edge Stability : very high
- > Grindability : good
- > Hot Hardness (red hardness) : high

Applications

> Twist Drills and Taps

Technical data

Material designation		Standards	
1.3344	SEL	4957	EN ISO
HS6-5-3	EN		

Chemical composition (wt. %)

С	Si	Mn	Cr	Мо	V	w
1.21	0.25	0.3	4.1	5	2.9	6.2





Material characteristics


	Compressive strength	Grindability	Red hardness	Toughness	Wear resistance	Edge Stability
BÖHLER S607	***	***	***	**	***	***
BÖHLER S200	***	**	***	**	***	**
BÖHLER S400	***	***	***	***	**	**
BÖHLER S401	**	***	**	***	**	***
BÖHLER S404	**	***	**	***	**	**
BÖHLER S405	***	***	**	***	**	**
BÖHLER S430	**	***	**	***	**	**
BÖHLER S500	****	***	****	**	***	***
BÖHLER S600	***	***	***	**	**	***
BÖHLER S601	***	***	***	**	**	***
BÖHLER S630	***	***	***	**	**	***
BÖHLER S705	***	***	****	**	**	****
BÖHLER S730	***	***	****	**	**	****

Delivery condition

Annealed	
Hardness (HB)	max. 280
Tensile Strength (N/mm ²)	max. 6,551

Heat treatment


		Quester lie distance distance (40, 0000 / b (50, 0005 / b)) to supress (00000 (444.005)) size
Temperature	770 to 840 °C	Controlled slow cooling in furnace (10 - 20°C / h (50 - 68°F / h)) to approx. 600°C (1110°F), air cooling.
Stress relieving		
Temperature	600 to 650 °C	Slow cooling furnace. To relieve stresses set up by extensive machining or in tools of intricate shape. After through heating, hold in neutral atmosphere for 1 to 2 hours.
Hardening and T	empering	
Temperature	1,190 to 1,230 °C	Salt bath, vacuum Preheating: 1st stage ~ 500 °C, 2nd stage ~ 850 °C, 3rd stage ~1050 °C Austenitising: 1190 - 1230 °C, holding time after complete heating 80 seconds, maximum 150 seconds, to avoid material damage due to overheating. Quenching: oil, warm bath (500 - 550 °C), gas
		Oleve her time to the meride a term and the investigation of the sector distinct of the Development of the








Continuous cooling CCT curves



Quantitative phase diagram



Kühlzeit von 800°C auf 500°C in Sek. / Cooling time in sec. from 800°C to 500°C (1472 - 932°F)


- Austenitising temperature: 1210°C (2210°F) Holding time: 180 seconds
- A....Austenite B....Bainite K....Carbide P....Perlite M....Martensite RA...Retained Austenite

- A....Austenite B....Bainite K....Carbide P....Perlite M....Martensite RA....Retained Austenite
- 1....Edge or Face 2....Core 3....Jominy test: distance from quenched end





Tempering Chart



Hardening temperature: 1220°C (2228°F)

Holding time 3 x 2 hours Specimen size: square 25 mm

Physical Properties

Temperature (°C)	20
Density (kg/dm ³)	8.1
Thermal conductivity (W/(m.K))	19
Specific heat (kJ/kg K)	0.46
Spec. electrical resistance (Ohm.mm ² /m)	0.54
Modulus of elasticity (10 ³ N/mm ²)	217

Thermal Expansions between 20°C | 68°F and ...

Temperature (°C)	100	200	300	400	500	600	700
Thermal expansion (10 ⁻⁶ m/(m.K))	11.5	11.7	12.2	12.4	12.7	13	12.9

If other available product variants are listed in addition to long products, please note that these may differ in terms of melting process, technical data, delivery and surface condition as well as available product dimensions. For mandatory technical specifications, other requirements and dimensions, please contact our regional voestalpine BÖHLER sales companies. The data contained in this brochure is merely for general information and therefore shall not be binding on the company. We may be bound only through a contract explicitly stipulating such data as binding. Measurement data are laboratory values and can deviate from practical analyses. The manufacture of our products does not involve the use of substances detrimental to health or to the ozone layer.

voestalpine BÖHLER Edelstahl GmbH & Co KG

Mariazeller Straße 25 8605 Kapfenberg, AT T. +43/50304/20-0 E. info@bohler-edelstahl.at https://www.voestalpine.com/bohler-edelstahl/de/

